





CUSTOM RANGE FOR REQUEST

Item No	Axis	Range		Resolution		Accuracy		Weight	Preset	Go/NoGo	Max/Min	Formula	Timer	Temp comp	Linear corr	Calibr date	Recharge	Memory	WIRELESS	USB	Display	
		X	Z	X	Z	X	Z															
		mm	mm	mm	mm	mm	mm															
27720902	1D	0-900	0-12	0.0001			±0,030	7.0	•	•	•	•	•	•	•	•	•	Folders / 2000 val	Long range / HID	USB HID / Update	Touchscreen 2.4"	
27720900	2D					0,01				7.2	•	•	•	•	•	•	•					•
27721802	1D	0-1800	0-12				±0,060	11.5	•	•	•	•	•	•	•	•	•					
27721800	2D					0,01				11.7	•	•	•	•	•	•	•					•
27722802	1D	0-2800	0-25				±0,004	20.5	•	•	•	•	•	•	•	•	•					
27722800	2D					0,01				20.7	•	•	•	•	•	•	•					•
27723802	1D	0-3800	0-50				±0,006	24.5	•	•	•	•	•	•	•	•	•					
27723800	2D					0,01				25	•	•	•	•	•	•	•					•
2D LASER MACROPROFILE STAND																						
27720907	2D	0-900	0-8	0,01	0.002	±0,030		7.0	•	•	•	•	•	•	•	•	•	Folders / 2000 val	Long range / HID	USB HID / Update	Touchscreen 2.4"	
27720908	2D						0-40	0,01		7.2	•	•	•	•	•	•	•					•
27721807	2D	0-1800	0-8			0.002	±0,060	11.5	•	•	•	•	•	•	•	•	•					
27721808	2D								0-40	0,01		11.7	•	•	•	•	•					•
27722807	2D	0-2800	0-8			0.002	±0,100	20.5	•	•	•	•	•	•	•	•	•					
27722808	2D								0-40	0,01		20.7	•	•	•	•	•					•
27723807	2D	0-3800	0-8			0.002	±0,160	24.5	•	•	•	•	•	•	•	•	•					•
27723808	2D								0-40	0,01		25	•	•	•	•	•					•

PIPE STRAIGHTNESS CONTROL COMPUTERIZED STAND



0,1µm

PAT.UA521681
PAT.UA140992

Item No	Axis	Range		Resolution	Accuracy		Weight	Preset	Go/NoGo	Max/Min	Formula	Timer	Temp comp	Linear corr	Calibr date	Recharge	Memory	WIRELESS	USB	Display
		X	Z		X	Z														
		mm	mm		mm	mm														
27520900	2D	0-900	0-12	0,0001	±0,040	±0,002	10	•	•	•	•	•	•	•	•	•	•	•	•	•
27521800		0-1800			±0,080	±0,002	15	•	•	•	•	•	•	•	•	•	•	•	•	•
27522800		0-2800			±0,120	±0,002	35	•	•	•	•	•	•	•	•	•	•	•	•	•